





Mini circuit breaker, Homeline, 50A, 2 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL

HOM250CP

Product availability: Stock - Normally stocked in distribution facility

Price*: 60.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	50 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 8AWG 2 (aluminium/copper)
Type Of Packing	Consumer packaging

Complementary

Tightening Torque	40.71 lbf.in (4.6 N.m) (AWG 8AWG 2)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For 104 °F (40 °C) Operation

Ordering and shipping details

Category	US10CPH01346
Discount Schedule	ОСРН
Gtin	047569062797
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	3.10 in (7.874 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	11.20 oz (317.515 g)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	1800
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1330.00 lb(US) (603.277 kg)
Unit Type Of Package 3	BB1
Number Of Units In Package 3	5
Package 3 Height	3.10 in (7.874 cm)
Package 3 Width	3.10 in (7.874 cm)
Package 3 Length	10.20 in (25.908 cm)
Package 3 Weight	3.65 lb(US) (1.656 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations