





Load center, Homeline, 1 phase, 40 spaces, 80 circuits, 200A convertible main breaker, PoN, NEMA1, Qwik-grip, value pack

HOM4080M200PQCVP

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,218.15 USD

### Main

Product Type	Load Center	
Marketing Trade Name	Homeline	
Load Center Type	PoN Convertible Mains (breaker)	
Rated Current	200 A	
Number Of Spaces	40	
Maximum Number Of Single Pole Circuits	80	
Enclosure Rating	NEMA 1 indoor	
Cover Type	Combination flush/surface cover	
Provided Equipment	Circuit-breaker 2) 1P 20 A 120/240 V AC Circuit-breaker 1) 2P 100 A 120/240 V AC main supply ready assembled Circuit-breaker 1) 2P 30 A 120/240 V AC Load center 1) Qwik grip assembly kit 1)	

### Complementary

Max Short Circuit Current Rating	10 kA
Maximum Number Of Tandem Breakers	40
Number Of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 4250 kcmil aluminium/copper
Ground Bar	Grounding bar (ordered separately)
Enclosure Material	Welded galvannealed steel
Surface Finish	Baked enamel Gray
Box Number	12Q
Bus Rated Current	225.0 A
Height	39.37 in (1000 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

### **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For 23 °F (-5 °C)
Operation 23 °F (-5 °C)

# Ordering and shipping details

Category	US1DE3C00185
Discount Schedule	DE3C
Gtin	785901613879
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.43 in (13.8 cm)
Package 1 Width	16.10 in (40.9 cm)
Package 1 Length	42.01 in (106.7 cm)
Package 1 Weight	40.59 lb(US) (18.411 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	18
Package 2 Height	38.00 in (96.52 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	755.00 lb(US) (342.462 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov