

Load center, Homeline, 1 phase, 40 spaces, 80 circuits, 200A convertible main breaker, PoN, NEMA1, gnd bar, bulk pack

HOM4080M200PTBP

(!) Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Load Center	
Marketing Trade Name	Homeline	
Load Center Type	PoN Convertible Mains (breaker)	
Rated Current	200 A	
Number Of Spaces	40	
Maximum Number Of Single Pole Circuits	80	
Enclosure Rating	NEMA 1 indoor	
Cover Type	Surface cover Order separately	
Electrical Connection	Lugs	
Provided Equipment	Circuit-breaker 1) 2P 200 A 120/240 V AC main supply ready assembled Grounding bar 1) ready assembled	

Complementary

Max Short Circuit Current Rating	22 kA
Maximum Number Of Tandem Breakers	40
Number Of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 4250 kcmil aluminium/copper
Wiring Configuration	3-wire
Busbar Material	Tin plated aluminium: busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel Gray
Box Number	12
Type Of Packing	Bulk
Height	39.37 in (1000 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UI listed file F-6294

Ordering and shipping details

	· · · · ·
Category	US1DE3C00045
Discount Schedule	DE3C
Gtin	785901977544
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	39.41 in (100.1 cm)
Package 1 Width	3.82 in (9.7 cm)
Package 1 Length	14.29 in (36.3 cm)
Package 1 Weight	22.00 lb(US) (9.979 ka)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov