





Load center, Homeline, 1 phase, 4 spaces, 8 circuits, 125A fixed main lugs, NEMA3R, gnd bar

HOM48L125GRB

Product availability: Stock - Normally stocked in distribution

Price\*: 137.00 USD

### Main

Product Type	Load Center
Marketing Trade Name	Homeline
Load Center Type	Fixed Mains (lugs)
Rated Current	125 A
Number Of Spaces	4
Maximum Number Of Single Pole Circuits	8
Enclosure Rating	NEMA 3R outdoor
Cover Type	Surface cover
Electrical Connection	Lugs
Provided Equipment	Grounding bar 1)

### Complementary

Max Short Circuit Current Rating	10 kA
Maximum Number Of Tandem Breakers	4
Number Of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 14AWG 2/0 copper AWG 12AWG 2/0 aluminium
Ground Bar	Grounding bar included (not installed)
Wiring Configuration	3-wire
Busbar Material	Tin plated aluminium: busbar
Enclosure Material	Welded galvannealed steel
Surface Finish	Baked enamel Gray
Box Number	15R
Bus Rated Current	125.0 A
Height	14.80 in (376 mm)
Width	8.90 in (226 mm)
Depth	4.25 in (108 mm)

#### **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL listed file E-6294

# Ordering and shipping details

Category	US1DE3C00149
Discount Schedule	DE3C
Gtin	785901484370
Returnability	Yes
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.80 in (12.192 cm)
Package 1 Width	10.30 in (26.162 cm)
Package 1 Length	16.10 in (40.894 cm)
Package 1 Weight	11.05 lb(US) (5.012 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	80
Package 2 Height	37.00 in (93.98 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	924.00 lb(US) (419.119 kg)

### **Contractual warranty**

Warranty Lifetime



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov