





Replacement cover, Homeline, for 24 space load center, combination flush and surface, gray

HOMC24UC

Product availability: Stock - Normally stocked in distribution facility

Price*: 111.00 USD

Main

Product Type	Load Center Cover
Marketing Trade Name	Homeline
Cover Type	Combination flush/surface cover

Complementary

Number Of Spaces	24
Surface Finish	Baked enamel Gray
Height	27.24 in (691.90 mm)
Width	15.44 in (392.18 mm)
Tightening Torque	Screw 2.3 N.m

Ordering and shipping details

Category	US10DE500183
Discount Schedule	0DE5
Gtin	785901077534
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.30 in (3.302 cm)
Package 1 Width	15.70 in (39.878 cm)
Package 1 Length	27.80 in (70.612 cm)
Package 1 Weight	9.96 lb(US) (4.518 kg)

Contractual warranty

Warranty Lifetime

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations