





Enclosed circuit breaker, Homeline, 2 pole, 50A, NEMA 3R, ground fault interrupt

HOME250SPA

Product availability: Stock - Normally stocked in distribution facility

Price*: 473.00 USD

Main

Product Type	Enclosed circuit breaker	
Range Of Product	Homeline	
Load Center Type	Main lugs	

Complementary

Current Rating	50 A
Interrupt Rating	10 kA
Number Of Spaces	2
Maximum Number Of Single Pole Circuits	4
Number Of Phases	1 phase
Enclosure Rating	NEMA 3R outdoor
Breaker Compatibility	Circuit breaker HOM-GFI 2P
Provided Equipment	Circuit-breaker 1) 2P 50 A 120/240 V AC ready assembled
Product Certifications	UL CSA
Wiring Configuration	3-wire
Wire Size	AWG 8AWG 6 aluminium/copper
Surface Finish	Baked enamel Gray
Voltage Rating	120/240 V AC
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Box Number	1R
Cover Type	Surface cover
Enclosure Material	Welded galvannealed steel
Height	9.37 in (238 mm)
Width	4.88 in (124 mm)
Depth	4.02 in (102 mm)

Ordering and shipping details

Category	US1DE3C00185
Discount Schedule	DE3C

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	785901230540	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.10 in (10.414 cm)
Package 1 Width	5.30 in (13.462 cm)
Package 1 Length	9.60 in (24.384 cm)
Package 1 Weight	6.13 lb(US) (2.78 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	6.00 in (15.24 cm)
Package 2 Width	10.30 in (26.162 cm)
Package 2 Length	17.80 in (45.212 cm)
Package 2 Weight	24.60 lb(US) (11.158 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	80
Package 3 Height	22.00 in (55.88 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	532.00 lb(US) (241.311 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov