Product data sheet

Specifications







Tandem circuit breaker, Homeline, 2 x 1 pole at 15A, 1 x 2 pole at 20A, 120/240VAC, 10kA AIR, plug in, UL

HOMT1515220

Product availability: Stock - Normally stocked in distribution facility

Price*: 120.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A 20 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	1P 2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2
Circuit Breaker Type	Quad tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 14AWG 8 (aluminium/copper)

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 8)	
Height	3.13 in (79.50 mm)	
Width	2 in (50.80 mm)	
Depth	2.98 in (75.69 mm)	

Environment

Ambient Air Temperature For 104 °F (40 °C) Operation

Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901101000
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of	Origin	
------------	--------	--

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.30 in (8.382 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	3.10 in (7.874 cm)
Package 1 Weight	13.44 oz (381.018 g)

Contractual warranty

Warranty

Lifetime

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations