





Tandem circuit breaker, Homeline, 1 x 1 pole at 15A, 1 x 1 pole at 20A, 120/240VAC, 10kA AIR, plug in, UL

HOMT1520

Product availability: Stock - Normally stocked in distribution facility

Price*: 52.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A 15 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Short Circuit Current Rating	10 kA
Number Of Spaces	1
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 12AWG 8 (aluminium)

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For 104 °F (40 °C)

Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901065418
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	6.88 oz (195.045 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	10.90 in (27.686 cm)
Package 2 Width	7.80 in (19.812 cm)
Package 2 Length	17.30 in (43.942 cm)
Package 2 Weight	45.19 lb(US) (20.498 kg)

Contractual warranty

Warranty	Lifetime
----------	----------



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Pro-active China Rons declaration (out of China Rons legal scope)
Product Environmental Profile
No need of specific recycling operations