Product data sheet

Specifications







Tandem circuit breaker, Homeline, 2 x 1 pole at 20A, 1 x 2 pole at 50A, 120/240VAC, 10kA AIR, plug in, UL

HOMT2020250

Product availability: Stock - Normally stocked in distribution facility

Price*: 120.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A 50 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	1P 2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2
Circuit Breaker Type	Quad tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 14AWG 6 (copper) 1 x AWG 12AWG 6 (aluminium) 1 x AWG 12AWG 8 (aluminium)

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.02 in² (2.510 mm²) (AWG 16AWG 14) 35.40 lbf.in (4.0 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For 104 °F (40 °C) Operation

Ordering and shipping details

Category	US1DE3D00046	
Discount Schedule	DE3D	
Gtin	785901377054	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	Yes	
Country Of Origin	US	

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	3.10 in (7.874 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	13.60 oz (385.554 g)

Contractual warranty

Warranty

Lifetime

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations