

Product data sheet

Specifications



Quad tandem circuit breaker,
Homeline, 1 x 2 pole at 15A, 1 x 2
pole at 20A, 120/240VAC, 10kA
AIR, plug in, UL

HOMT215220

Product availability: Stock - Normally stocked in distribution facility

Price*: 130.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A 20 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2.0
Circuit Breaker Type	Quad tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 14...AWG 8 (aluminium/copper)

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in² (2.5...6 mm²) (AWG 14...AWG 8)
Height	3.13 in (79.50 mm)
Width	1.97 in (50.04 mm)
Depth	3.23 in (82.04 mm)

Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901969181
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8 cm)
Package 1 Width	1.97 in (5 cm)
Package 1 Length	3.23 in (8.2 cm)
Package 1 Weight	16.00 oz (453.592 g)

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)