

# Product data sheet

Specifications



Quad tandem circuit breaker,  
Homeline, 1 x 2 pole at 25A, 1 x 2  
pole at 30A, 120/240VAC, 10kA  
AIR, plug in, UL

HOMT225230

Product availability: Stock - Normally stocked in distribution facility

Price\*: 130.00 USD

## Main

|                              |   |
|------------------------------|---|
| Product                      | Miniature circuit-breaker               |
| Range                        | Homeline                                |
| Current Rating               | 25 A<br>30 A                            |
| Certifications               | UL Listed                               |
| Voltage Rating               | 120/240 V AC                            |
| Mounting Type                | Plug-in                                 |
| Number Of Poles              | 2P                                      |
| Short Circuit Current Rating | 10 kA                                   |
| Number Of Spaces             | 2.0                                     |
| Circuit Breaker Type         | Quad tandem                             |
| Ratings                      | HACR rated                              |
| Electrical Connection        | Box lugs                                |
| Wire Size                    | 1 x AWG 14...AWG 8 ( aluminium/copper ) |

## Complementary

|                   |   |
|-------------------|---|
| Tightening Torque | 35.40 lbf.in (4.0 N.m) 0.00...0.02 in² (2.5...10 mm²) (AWG 16...AWG 14)<br>35.40 lbf.in (4.0 N.m) 0.01...0.03 in² (4...20 mm²) (AWG 12...AWG 4) |
| Height            | 3.13 in (79.50 mm)  |
| Width             | 1.97 in (50.04 mm)  |
| Depth             | 3.23 in (82.04 mm)  |

## Environment

|                                       |                |
|---------------------------------------|----------------|
| Ambient Air Temperature For Operation | 104 °F (40 °C) |
|---------------------------------------|----------------|

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US1DE3D00046 |
| Discount Schedule | DE3D         |
| Gtin              | 785901970385 |
| Returnability     | Yes          |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                   |    |
|-------------------|----|
| Country Of Origin | US |
|-------------------|----|

Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type Of Package 1       | PCE                  |
| Number Of Units In Package 1 | 1                    |
| Package 1 Height             | 3.15 in (8 cm)       |
| Package 1 Width              | 1.97 in (5 cm)       |
| Package 1 Length             | 3.23 in (8.2 cm)     |
| Package 1 Weight             | 16.00 oz (453.592 g) |

# Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

|   |                            |   |
|---|----------------------------|---|
|  | Toxic Heavy Metal Free     |   |
|  | Mercury Free               |   |
|  | Rohs Exemption Information | <a href="#">Yes</a>   |
|   |                            |   |
| Reach Regulation  |                            | <a href="#">REACH Declaration</a>   |
|   |                            |   |
| Eu Rohs Directive   |                            | Compliant<br><a href="#">EU RoHS Declaration</a>  |
|   |                            |   |
| China Rohs Regulation   |                            | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |