





Safety switch, heavy duty, non fusible, 30A, 3 wires, 3 pole, 30hp, 600VAC/DC, NEMA 3R, bolt on hub provision

HU361RB



(!) Discontinued on: Jun 23, 2023

Product availability: Stock - Normally stocked in distribution facility

#### Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Non-fusible disconnect	
Factory Installed Neutral	None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	30 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 3R galvannealed steel	
Motor Power Hp	5 hp at 240 V AC 50-60 Hz for 1 phase motors 10 hp at 240 V AC 50-60 Hz for 3 phase motors 7.5 hp at 480 V AC 50-60 Hz for 1 phase motors 20 hp at 480 V AC 50-60 Hz for 3 phase motors 10 hp at 600 V AC 50-60 Hz for 1 phase motors 30 hp at 600 V AC 50-60 Hz for 1 phase motors 5 hp at 250 V DC 15 hp at 600 V DC	

## **Complementary**

-	
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 12AWG 6 aluminium AWG 14AWG 6 copper
Tightening Torque	45 lbf.in (5.08 N.m) 0.02 in² (13.3 mm²) (AWG 6) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)
Depth	4.86 in (123.44 mm)
Width	7.55 in (191.77 mm)
Height	14.88 in (377.95 mm)
Net Weight	8.82 lb(US) (4 kg)

### **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10DE100009	
Discount Schedule	0DE1	
Gtin	785901505600	
Returnability	Yes	
Country Of Origin	US	

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.20 in (13.208 cm)	
Package 1 Width	7.90 in (20.066 cm)	
Package 1 Length	16.40 in (41.656 cm)	
Package 1 Weight	8.16 lb(US) (3.701 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	120	
Package 2 Height	46.00 in (116.84 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	1008.00 lb(US) (457.221 kg)	

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov