Product data sheet

Specifications



Safety switch, heavy duty, non fusible, 100A, 3 wire, 3 pole, 100HP, 600V AC/DC, NEMA 12

HU363AWK

Discontinued on: Nov 22, 2023

① Discontinued

Product availability: Stock - Normally stocked in distribution facility

Μ	ai	n
		•••

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Non-fusible disconnect	
Factory Installed Neutral	None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	100 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 3R/12 galvannealed steel	
Motor Power Hp	20 hp at 240 V AC 50-60 Hz for 1 phase motors 40 hp at 240 V AC 50-60 Hz for 3 phase motors 40 hp at 480 V AC 50-60 Hz for 1 phase motors 75 hp at 480 V AC 50-60 Hz for 3 phase motors 40 hp at 600 V AC 50-60 Hz for 1 phase motors 100 hp at 600 V AC 50-60 Hz for 3 phase motors 20 hp at 250 V DC 50 hp at 600 V DC	

Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 12AWG 1/0 aluminium AWG 14AWG 1/0 copper
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 1AWG 3/0) 45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)
Depth	7 in (177.80 mm)
Width	10.5 in (266.70 mm)
Height	20.5 in (520.70 mm)
Net Weight	19.84 lb(US) (9 kg)

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

UL listed file E2875

Ordering and shipping details

Category	US10DE100113
Discount Schedule	0DE1
Gtin	785901505754
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.30 in (18.542 cm)
Package 1 Width	10.60 in (26.924 cm)
Package 1 Length	23.50 in (59.69 cm)
Package 1 Weight	19.22 lb(US) (8.72 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov