





Safety switch, heavy duty, non fusible, 100A, 3 pole, 100hp, 600VAC/DC, NEMA 4X krydonTM fiberglass polyester

HU363DX

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 8,438.00 USD

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	onnect Type Non-fusible disconnect	
Factory Installed Neutral	y Installed Neutral None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	100 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	ating NEMA 4X Krydon - compression molded fiberglass reinforced polyester	
Motor Power Hp	75 hp at 480 V AC 50-60 Hz for 3 phase motors 100 hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V DC	

Complementary

Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	3-wire	
Wire Size	AWG 12AWG 1/0 aluminium AWG 14AWG 1/0 copper	
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 1AWG 3/0) 45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)	
Depth	8.6 in (218.44 mm)	
Width	11.4 in (289.56 mm)	
Height	25.25 in (641.35 mm)	
Net Weight	37.92 lb(US) (17.2 kg)	

Environment

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100111	
Discount Schedule	0DE1	
Gtin	785901549130	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.24 in (64.1 cm)
Package 1 Width	11.42 in (29 cm)
Package 1 Length	8.58 in (21.8 cm)
Package 1 Weight	54.65 lb(US) (24.789 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov