

Product data sheet

Specifications

SQUARE D

Green Premium™



Safety switch, heavy duty, non fusible, 200A, 3 wire, 3 pole, 150HP, 600V AC/DC, NEMA 12

HU364AWK

⚠ Discontinued on: Nov 22, 2023

⚠ Discontinued

Product availability: Stock - Normally stocked in distribution facility

Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Phase	3 phase
Number Of Poles	3
Current Rating	200 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R/12 galvanized steel
Motor Power Hp	15 hp at 240 V AC 50-60 Hz for 1 phase motors 60 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 480 V AC 50-60 Hz for 1 phase motors 125 hp at 480 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V AC 50-60 Hz for 1 phase motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 40 hp at 250 V DC 50 hp at 600 V DC

Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 6...250 kcmil copper or aluminium
Tightening Torque	275 lbf.in (31.07 N.m) 0.02...0.20 in ² (13.3...127 mm ²) (AWG 6...250 kcmil)
Depth	8.75 in (222.25 mm)
Width	18.63 in (473.20 mm)
Height	29 in (736.60 mm)
Net Weight	52.01 lb(US) (23.59 kg)

Environment

Certifications	UL listed file E2875
----------------	----------------------

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US10DE100113
Discount Schedule	0DE1
Gtin	785901505778
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.20 in (23.368 cm)
Package 1 Width	19.50 in (49.53 cm)
Package 1 Length	32.50 in (82.55 cm)
Package 1 Weight	51.33 lb(US) (23.283 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov