

Product data sheet

Specifications



Switchgear, HVL, single, 600A, 15kV, 3 pole, 10 to 100E DIN/E current limit fuse, NEMA 3R

HVL315DEW1

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 23,978.00 USD

Main

| | |
|--------------------|-------------------------------|
| Product | Switched fuse mechanism |
| Included Accessory | Enclosure heater |
| Not Included | fuse to be ordered separately |

Complementary

| | |
|------------------------------------|---|
| Protection Type | Fuse current limiter |
| Associated Fuse Rating | 10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E |
| Line Rated Current | 600 A |
| Momentary Amperes Asymmetrical | 40 kA |
| Frequency | 50/60 Hz |
| Number Of Poles | 3P |
| Highest Voltage For Equipment (Um) | 15 kV |
| Basic Inulation Level | 90 kV |
| Enclosure Rating | NEMA 3R |
| Electrical Connection | Lugs |
| Type Of Installation | Outdoor |
| Wire Gauge | AWG 2...600 kcmil aluminium/copper |
| Enclosure Width | 38 in (965.20 mm) |
| Enclosure Depth | 60 in (1524.00 mm) |
| Enclosure Height | 97 in (2463.80 mm) |

Environment

| | |
|------------------------|------------------|
| Product Certifications | cUL UL Listed |
|------------------------|------------------|

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|---------------|
| Category | US1PE5A07945 |
| Discount Schedule | PE5A |
| Gtin | 3606486276389 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

| | |
|------------------------------|-----------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 1200.00 lb(US) (544.311 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|