

# Product data sheet

Specifications



Switchgear, HVL, single, 600A, 15kV, 125 to 200E current limit fuse, transformer disconnect, left, NEMA 1

HVL415DEGL2

Product availability: Stock - Normally stocked in distribution facility

Price\*: 20,614.00 USD

## Main

Product	Transformer Disconnect
Not Included	fuse to be ordered separately
Device Application	Transformer left side

## Complementary

Protection Type	Fuse current limiter
Associated Fuse Rating	125 A E 150 A E 175 A E 200 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Full Load Current	300 A
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	15 kV
Basic Inulation Level	95 kV
Enclosure Rating	NEMA 1
Electrical Connection	Lugs
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in (965.20 mm)
Enclosure Depth	54.5 in (1384.30 mm)
Enclosure Height	90 in (2286.00 mm)

## Environment

Product Certifications	UL Listed cUL
------------------------	------------------

## Ordering and shipping details

Category	07944-15KV DIGEST HVL NEMA 1
Discount Schedule	PE5A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	3606486276532
Returnability	No

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	1200.00 lb(US) (544.311 kg)

### Contractual warranty

Warranty	18 months
----------	-----------