

Product data sheet

Specifications



Switchgear, HVL, single, 600A, 15kV, 125 to 200E current limit fuse, transformer disconnect, right, NEMA 1

HVL415DEGR2

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 30,921.00 USD

Main

Product	Transformer Disconnect
Not Included	fuse to be ordered separately
Device Application	Transformer right side

Complementary

Protection Type	Fuse current limiter
Associated Fuse Rating	125 A E 150 A E 175 A E 200 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Full Load Current	300 A
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	15 kV
Basic Inulation Level	95 kV
Enclosure Rating	NEMA 1
Electrical Connection	Lugs
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in (965.20 mm)
Enclosure Depth	54.5 in (1384.30 mm)
Enclosure Height	90 in (2286.00 mm)

Environment

Product Certifications	UL Listed cUL
------------------------	------------------

Ordering and shipping details

Category	US1PE5A07944
Discount Schedule	PE5A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	3606486276556
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	90.00 in (228.6 cm)
Package 1 Width	37.99 in (96.5 cm)
Package 1 Length	54.02 in (137.2 cm)
Package 1 Weight	1200.00 lb(US) (544.311 kg)

Contractual warranty

Warranty	18 months
----------	-----------