

Product data sheet

Specifications



Switchgear, HVL, duplex, 600A, 4.76kV, 10 to 450E current limit fuse, transformer disconnect, left, NEMA 3R

HVL505DEWLH

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 74,226.00 USD

Main

Product	Transformer Disconnect
Not Included	fuse to be ordered separately
Device Application	Transformer left side

Complementary

Protection Type	Fuse current limiter
Associated Fuse Rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E 250 A E 300 A E 400 A E 350 A E 500 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Full Load Current	300 A
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	4.76 kV
Basic Inulation Level	60 kV
Enclosure Rating	NEMA 3R
Electrical Connection	Lugs
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	76 in (1930.40 mm)
Enclosure Depth	60 in (1524.00 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Height	97 in (2463.80 mm)
------------------	--------------------

Environment

Product Certifications	UL Listed cUL
------------------------	------------------

Ordering and shipping details

Category	US1PE5A07943
Discount Schedule	PE5A
Gtin	3606486276648
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	2400.00 lb(US) (1088.622 kg)

Contractual warranty

Warranty	18 months
----------	-----------