

Product data sheet

Specifications



Switchgear, HVL, duplex, 600A, 15kV, 125 to 200E current limit fuse, transformer disconnect, right, NEMA 3R

HVL515DEWR2H

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 82,356.00 USD

Main

Product	Transformer Disconnect
Not Included	fuse to be ordered separately
Device Application	Transformer right side

Complementary

Protection Type	Fuse current limiter
Associated Fuse Rating	125 A E 150 A E 175 A E 200 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Full Load Current	300 A
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	15 kV
Basic Inulation Level	95 kV
Enclosure Rating	NEMA 3R
Electrical Connection	Lugs
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	76 in (1930.40 mm)
Enclosure Depth	60 in (1524.00 mm)
Enclosure Height	97 in (2463.80 mm)

Environment

Product Certifications	cUL UL Listed
------------------------	------------------

Ordering and shipping details

Category	US1PE5A07945
Discount Schedule	PE5A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	3606486276754
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	2800.00 lb(US) (1270.059 kg)

Contractual warranty

Warranty	18 months
----------	-----------