

Product data sheet

Specifications

SQUARE D



Switchgear, HVLcc, fused, 15kV, 600A, 14.75in W, top entry, transformer on right

HVLCCA14415DGR

⚠ Discontinued on: May 19, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|--------------------|-------------------------------|
| Product | Switched fuse mechanism |
| Application | A |
| Not Included | fuse to be ordered separately |
| Device Application | Transformer right side |

Complementary

| | |
|------------------------------------|---|
| Protection Type | Fuse current limiter |
| Associated Fuse Rating | 10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E |
| Line Rated Current | 600 A |
| Momentary Amperes Asymmetrical | 40 kA |
| Full Load Current | 300 A |
| Frequency | 50/60 Hz |
| Number Of Poles | 3P |
| Highest Voltage For Equipment (Um) | 15 kV |
| Basic Inulation Level | 95 kV |
| Enclosure Rating | NEMA 1 |
| Electrical Connection | Lugs |
| Wire Gauge | AWG 2...350 kcmil 2 aluminium/copper |
| Service Entry | OH |
| Enclosure Width | 14.75 in (374.65 mm) |
| Enclosure Depth | 37.25 in (946.15 mm) |
| Enclosure Height | 90 in (2286.00 mm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US1PE5A07948 |
| Discount Schedule | PE5A |
| Gtin | 3606486276839 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

| | |
|------------------------------|----------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 480.00 lb(US) (217.724 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|