

Product data sheet

Specifications



Switchgear, HVLcc, fused, 4.76kV, 600A, 14.75in W, bottom entry

HVLCCB14305D

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 29,088.00 USD

Main

Product	Switched fuse mechanism
Application	B
Not Included	fuse to be ordered separately

Complementary

Protection Type	Fuse current limiter
Associated Fuse Rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E 250 A E 300 A E 400 A E 350 A E 500 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	4.76 kV
Basic Inulation Level	60 kV
Enclosure Rating	NEMA 1
Electrical Connection	Lugs
Wire Gauge	AWG 2...350 kcmil 2 aluminium/copper
Service Entry	UG
Enclosure Width	14.75 in (374.65 mm)
Enclosure Depth	37.25 in (946.15 mm)
Enclosure Height	90 in (2286.00 mm)

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US1PE5A07948
Discount Schedule	PE5A
Gtin	3606486277027
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	480.00 lb(US) (217.724 kg)

Contractual warranty

Warranty	18 months
----------	-----------