

# Product data sheet

Specifications



Switchgear, HVLcc, 15kV, 600A,  
14.75in W, bottom entry,  
transformer on left

HVLCCB14515DGL

Product availability: Non-Stock - Not normally stocked in  
distribution facility

Price\*: 86,142.00 USD

## Main

|                    |                               |
|--------------------|-------------------------------|
| Product            | Switched fuse mechanism       |
| Application        | B                             |
| Not Included       | fuse to be ordered separately |
| Device Application | Transformer left side         |

## Complementary

|                                    |   |
|------------------------------------|---|
| Protection Type                    | Fuse current limiter  |
| Associated Fuse Rating             | 10 A E<br>15 A E<br>20 A E<br>25 A E<br>30 A E<br>40 A E<br>50 A E<br>65 A E<br>80 A E<br>100 A E<br>125 A E<br>150 A E<br>175 A E<br>200 A E |
| Line Rated Current                 | 600 A   |
| Momentary Amperes Asymmetrical     | 40 kA   |
| Full Load Current                  | 300 A   |
| Frequency                          | 50/60 Hz  |
| Number Of Poles                    | 3P  |
| Highest Voltage For Equipment (Um) | 15 kV   |
| Basic Inulation Level              | 95 kV   |
| Enclosure Rating                   | NEMA 1  |
| Electrical Connection              | Lugs  |
| Wire Gauge                         | AWG 2...350 kcmil 2 aluminium/copper  |
| Service Entry                      | UG  |
| Enclosure Width                    | 29.5 in (749.30 mm)   |
| Enclosure Depth                    | 37.25 in (946.15 mm)  |
| Enclosure Height                   | 90 in (2286.00 mm)  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US1PE5A07948  |
| Discount Schedule | PE5A          |
| Gtin              | 3606486277126 |
| Returnability     | No            |
| Country Of Origin | US            |

## Packing Units

|                              |                            |
|------------------------------|----------------------------|
| Unit Type Of Package 1       | PCE                        |
| Number Of Units In Package 1 | 1                          |
| Package 1 Weight             | 925.00 lb(US) (419.573 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|