# **Product data sheet**

Specifications





# integrated servo motor - 1.7 Nm - 6000 rpm - multiturn - with brake

ILM0702P02F0000

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 4,149.46 USD

### Main

Range Of Product	PacDrive 3
Product Or Component Type	Servo motor integrated drive
Device Short Name	ILM

## Complementary

[Us] Rated Supply Voltage	250700 V	
Continuous Stall Current	2.5 A	
Continuous Stall Torque	15.05 lbf.in (1.7 N.m)	
Peak Stall Torque	67.27 lbf.in (7.6 N.m)	
Nominal Output Power	720 W	
Nominal Torque	10.18 lbf.in (1.15 N.m)	
Nominal Speed	6000 rpm	
Maximum Current Irms	rrent Irms 11.8 A	
Line Rated Current	1.5 A	
Shaft End	Untapped	
Second Shaft	Without second shaft end	
Shaft Diameter	0.43 in (11 mm)	
Shaft Length	0.91 in (23 mm)	
Key Width	0.71 in (18 mm)	
Feedback Type	Absolute multiturn SinCos Hiperface	
Speed Feedback Resolution	128 periods	
Holding Brake	With	
Holding Torque	26.55 lbf.in (3 N.m) holding brake	
Mounting Support	International standard flange	
Motor Flange Size	2.76 in (70 mm)	
Torque Constant	0.76 N.m/A 248 °F (120 °C)	
Back Emf Constant	48 V/krpm 68 °F (20 °C)	
Number Of Motor Poles	6	
Rotor Inertia	0.51 kg.cm²	
Stator Resistance	4.2 Ohm 68 °F (20 °C) Ph/Ph 2.92 Ohm 248 °F (120 °C) Ph/N	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Stator Inductance	19 mH 68 °F (20 °C) Ph/Ph
	9.5 mH 248 °F (120 °C) Ph/N
Maximum Radial Force Fr	710 N 1000 rpm
	560 N 2000 rpm
	490 N 3000 rpm
	450 N 4000 rpm
	410 N 5000 rpm
	390 N 6000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	9.92 in (252 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	2.36 in (60 mm)
Centring Collar Depth	0.10 in (2.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)
Net Weight	8.16 lb(US) (3.7 kg)

### **Environment**

Ip Degree Of Protection IP54

## Ordering and shipping details

Category	US1PC5218351	
Discount Schedule	PC52	
Gtin	3606485293783	
Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	8.27 in (21.0 cm)	
Package 1 Width	7.09 in (18.0 cm)	
Package 1 Length	14.02 in (35.6 cm)	
Package 1 Weight	9.44 lb(US) (4.28 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov