## **Product data sheet**

Specifications





# integrated servo motor - 12.5 Nm - 2000 rpm - without brake - IP65

ILM1402P21A0000

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 11,988.76 USD

### Main

Range Of Product	PacDrive 3
Product Or Component Type	Servo motor integrated drive
Device Short Name	ILM

## **Complementary**

[Us] Rated Supply Voltage	250700 V
Continuous Stall Current	4.8 A
Continuous Stall Torque	110.63 lbf.in (12.5 N.m)
Peak Stall Torque	486.79 lbf.in (55 N.m)
Nominal Output Power	1910 W
Nominal Torque	80.54 lbf.in (9.1 N.m)
Nominal Speed	2000 rpm
Maximum Current Irms	24 A
Line Rated Current	3.7 A
Shaft End	Untapped
Second Shaft	Without second shaft end
Shaft Diameter	0.94 in (24 mm)
Shaft Length	1.97 in (50 mm)
Key Width	1.57 in (40 mm)
Feedback Type	Absolute single turn SinCos Hiperface
Speed Feedback Resolution	128 periods
Holding Brake	Without
Mounting Support	International standard flange
Motor Flange Size	5.51 in (140 mm)
Torque Constant	2.6 N.m/A 248 °F (120 °C)
Back Emf Constant	173 V/krpm 68 °F (20 °C)
Number Of Motor Poles	10
Rotor Inertia	12.68 kg.cm²
Stator Resistance	1.9 Ohm 68 °F (20 °C) Ph/Ph 1.32 Ohm 248 °F (120 °C) Ph/N
Stator Inductance	22 mH 68 °F (20 °C) Ph/Ph 11 mH 248 °F (120 °C) Ph/N

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum Radial Force Fr	2430 N 1000 rpm 1930 N 2000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	12.17 in (309 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	5.12 in (130 mm)
Centring Collar Depth	0.14 in (3.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.43 in (11 mm)
Circle Diameter Of The Mounting Holes	6.50 in (165 mm)
Net Weight	37.92 lb(US) (17.2 kg)

### **Environment**

Ip Degree Of Protection IP65

## Ordering and shipping details

Category	US1PC5218351
Discount Schedule	PC52
Gtin	3606485294957
Returnability	No
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.24 in (26.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	23.23 in (59.0 cm)
Package 1 Weight	50.99 lb(US) (23.13 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov