





PowerPact

PowerPact J

Circuit breaker, PowerPacT J, 250A, 3 pole, 600VAC, 18kA, lugs, Micrologic 3.2, 80%

JGL36250U31X

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 4,006.00 USD

Main Range

Product Name

Utilisation Category

Awg Gauge

Product Or Component Type	Circuit breaker
Device Application	Distribution
Complementary	
Line Rated Current	250 A
Number Of Poles	3P
Control Type	Toggle
Breaking Capacity Code	G
Breaking Capacity	65 kA 240 V AC 50/60 Hz UL 489 35 kA 480 V AC 50/60 Hz UL 489 18 kA 600 V AC 50/60 Hz UL 489 18 kA 250 V DC UL 489 20 kA 500 V DC UL 489
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz IEC 60947-3
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA 220/240 V AC 50/60 Hz IEC 60947-2 35 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 18 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Electronic, standard, MicroLogic 3.2, LI
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Trip Unit Name	MicroLogic 3.2
Protection Type	Overload protection Short-circuit protection
Suitability For Isolation	Yes IEC 60947-2

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

AWG 3/0...350 kcmil aluminium/copper terminals

Category A

Local Signalling	Ready 1 LED green)
	Alarm 1 LED 90 % Ir orange)
	Alarm 1 LED 105 % Ir red)
	Switched off (OFF) 1 trip indicator green)
	Switched on (OFF) 1 trip indicator green)
Mounting Mode	Unit mount lug)
Mounting Support	Lug
Electrical Connection	Lugs, line
	Lugs, load
Terminal Identifier	AL250JD
Long Time Pick-Up Adjustment	0.251 x ln
Range	U.25 I X III
Tightening Torque	224 27 lbf in /25 N m) 0.45 0.20 in² /05 195 mm²) /A\WC 2/0 250 komil\
	221.27 lbf.in (25 N.m) 0.150.29 in ² (95185 mm ²) (AWG 3/0350 kcmil)
Number Of Slots	2 auxiliary switch OF plug-in)
	1 alarm switch SD plug-in)
	1 overcurrent trip switch SDE plug-in)
	1 voltage release MN or MX plug-in)
	1 Voltage Telease Will of Wilk plug III)
Power Wire Stripping Length	0.98 in (25 mm)
Hainb	7.50: (404
Height	7.52 in (191 mm)
Width	4.09 in (104 mm)
Depth	3.39 in (86 mm)
Net Weight	5.29 lb(US) (2.4 kg)
Communication Interface	Modbus
	Ethernet
	Euromot
Circuit Breaker Application	HACR rated

Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating

Ordering and shipping details

Category	US10DE201107
Discount Schedule	0DE2
Gtin	785901125990
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.13 in (13.018 cm)
Package 1 Width	7.25 in (18.415 cm)
Package 1 Length	8.44 in (21.433 cm)
Package 1 Weight	5.18 lb(US) (2.35 kg)

Contractual warranty

May 19, 2024

Warranty 18 months

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration