





Safety switch, light duty, fusible, 30A, 3 wire, 2 poles, 1 neutral, 120VAC, Type 1

L211N

Product availability: Stock - Normally stocked in distribution facility

Price*: 72.00 USD

Main

Product	Single Throw Safety Switch	
Duty Rating	Light duty	
Device Application	Furnace Garages	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	Neutral (factory installed)	
Phase	3 phase	
Number Of Poles	2	
Current Rating	30 A	
Voltage Rating	240 V AC	
Nema Degree Of Protection	NEMA 1	
Motor Power Hp 0.5 hp at 120 V AC 50-60 Hz for 1 phase motors 2 hp at 120 V AC 50-60 Hz for 1 phase motors 1.5 hp at 240 V AC 50-60 Hz for 1 phase motors 3 hp at 240 V AC 50-60 Hz for 1 phase motors		

Complementary

Short-Circuit Current	10 kA	
Fuse Type	Plug	
Mounting Type	Surface	
Wiring Configuration	3-wire 3-wire	
Wire Size	AWG 14AWG 8 copper AWG 12AWG 8 aluminium	
Tightening Torque	30 lbf.in (3.39 N.m) 0.000.01 in² (2.0828.367 mm²) (AWG 14AWG 8) 30 lbf.in (3.39 N.m) 0.010.01 in² (3.3078.367 mm²) (AWG 12AWG 8)	
Depth	4 in (101.60 mm)	
Width	6.13 in (155.70 mm)	
Height	7.63 in (193.80 mm)	
Net Weight	3.00 lb(US) (1.36 kg)	

Environment

Product Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1DE1A00057	
Discount Schedule	DE1A	
Gtin	785901090526	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.50 in (13.97 cm)	
Package 1 Width	6.50 in (16.51 cm)	
Package 1 Length	ckage 1 Length 8.30 in (21.082 cm)	
Package 1 Weight	e 1 Weight 3.41 lb(US) (1.547 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	200	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	682.20 lb(US) (309.44 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov