# **Product data sheet**

Specifications





# reversing contactor - 575 V AC - 115 A - IEC

LC2D115L7

! Discontinued on: May 19, 2023

① Discontinued

#### Main

Range Of Product	TeSys D	
Product Or Component Type	Reversing contactor	
Device Short Name	LC2D	
Contactor Application	Motor control	
Utilisation Category	AC-3 AC-2 AC-4	
Control Circuit Type	AC	
Coil Type	Standard	
Poles Description	Description 3P	
Pole Contact Composition	ition 3 NO	

## Complementary

Assembly Style	Ready assembled	
Coil Technology	Without built-in bidirectional peak limiting diode suppressor	
Protective Cover	With	
Auxiliary Contact Composition	1 NO + 1 NC	
Interlocking Type	Mechanical	
Overvoltage Category	III	
Mounting Support	Plate Rail	
Associated Fuse Rating	10 A gG for control circuit conforming to IEC 60947-5-1	
Mechanical Durability	8000000 cycles	
Height	6.22 in (158 mm)	
Width	10.47 in (266 mm)	
Depth	5.83 in (148 mm)	
Net Weight	14.00 lb(US) (6.35 kg)	

#### **Environment**

Apr 19, 2024

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	EN 60947-4-1 IEC 60947-4-1 CSA C22.2 No 14 IEC 60947-5-1 UL 508 EN 60947-5-1
Product Certifications	DNV RINA BV CCC CSA UL GL GOST LROS (Lloyds register of shipping)
Ambient Air Temperature For Operation	23140 °F (-560 °C)
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)

## Ordering and shipping details

Category	22354-CTR,TESYS D,OPEN,9-38A AC
Discount Schedule	112
Gtin	3389110737912
Returnability	No
Country Of Origin	CZ

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.06 in (23 cm)
Package 1 Width	12.40 in (31.5 cm)
Package 1 Length	14.57 in (37 cm)
Package 1 Weight	14.33 lb(US) (6.5 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Mercury Free	
	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov