

Product data sheet

Specifications



12A FVNR COMBO 1/12/3R CPT FLA 0.6

LE1U16BAV81NCP1

Price*: 3,139.00 USD

! Discontinued

Main

Product Or Component Type	Self-protected combination starter
Range Of Product	TeSys U Self-Protected Combination Motor Controller
[Ue] Rated Operational Voltage	480Y/277 V 208 V AC 240 V
Phase	3 phase
Network Rated Voltage	460 V AC not for use on 480V Delta systems 7.5 hp maximum
Thermal Overload Type	Solid state advanced class 10 0.15...0.6 A
Communication Port Protocol	Without
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz
Control Circuit	Control circuit transformer 2 fuses (primary), 1 fuse (secondary)
Control Type	Selector switch HAND-OFF-AUTO)
Local Signalling	Red indicator on LED

Complementary

Nema Degree Of Protection	NEMA 1/12/3R
Enclosure Material	Painted sheet steel
Enclosure Type	Standard size
Enclosure Accessory Description	With external reset
Product Certifications	NOM CE UL Listed ANSI CSA
Auxiliary Contact Composition	1 NO + 1 NC
Poles Description	3P
Motor Starter Type	Non reversing
Electrical Connection	Screw-clamp terminals
Disconnecter Device Type	Self-protected combination controller 12 A

Ordering and shipping details

Category	22319-ENCLOSED TESYS U COMB STR 32A
Discount Schedule	I11

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
---------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	20.03 lb(US) (9.085 kg)