

Product data sheet

Specifications



Prewired connection, LU2B, Tesys Ultra

LU9MRL

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 57.00 USD

Main

| | |
|---------------------------|---------------------------|
| Range | TeSys |
| Device Short Name | LU9M |
| Product Or Component Type | Pre-wired coil connection |
| Product Compatibility | LU2B.. |

Complementary

| | |
|-------------------|---|
| Bus Type | Advantys STB Profibus DP DeviceNet CANopen |
| Net Weight | 0.99 lb(US) (0.45 kg) |
| Tightening Torque | Control circuit 7.08...10.62 lbf.in (0.8...1.2 N.m) flat 0.20 in (5 mm) Control circuit 7.08...10.62 lbf.in (0.8...1.2 N.m) Philips No 2 0.20 in (5 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) flat 0.24 in (6 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) Philips No 2 0.24 in (6 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) pozidriv No 2 0.24 in (6 mm) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US10I1122399 |
| Discount Schedule | 0I11 |
| Gtin | 3389119407083 |
| Returnability | No |
| Country Of Origin | CZ |

Packing Units

| | |
|------------------------------|--------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.18 in (3.0 cm) |
| Package 1 Width | 5.12 in (13.0 cm) |
| Package 1 Length | 8.66 in (22.0 cm) |
| Package 1 Weight | 1.09 oz (31.0 g) |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 30 |
| Package 2 Height | 5.91 in (15.0 cm) |
| Package 2 Width | 11.81 in (30.0 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|------------------------|
| Package 2 Length | 15.75 in (40.0 cm) |
| Package 2 Weight | 3.05 lb(US) (1.385 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|---|--|-----|
|  | Reach Free Of Svhc | |
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | REACH Declaration | |
| Eu Rohs Directive | Compliant EU RoHS Declaration | |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov | |