

# Product data sheet

Specifications



Surge protection module,  
Surgelogic, MA, 240kA, 208Y/120  
VAC, 3 phase, 4 wire, SPD type 1

MA2IBA241

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

## Main

Product	Surge protection module
Range	Surgelogic
Device Short Name	IBA
Accessory Category	Replacement part

## Complementary

Voltage Rating	208Y/120 V AC
Mcov	150 V
Sccr	200 kA
Surge Current	240 kA per phase
Nominal Discharge Current	20 kA
Number Of Phases	3 phase
Wiring Configuration	4-wire
Connection	Terminals
Local Signalling	Status LED green normal operation
Provided Equipment	Alarm enable/disable switch
Mounting Support	Panel mounting
Height	6.25 in (158.8 mm)
Width	9.92 in (252 mm)
Depth	2.69 in (68.3 mm)

## Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 1
Enclosure Material	Black Plastic
Standards	UL 1449:ed. 4 UL 1283:ed. 5 CSA C22.2 No 8:1986 ANSI/IEEE C62.41 ANSI/IEEE C62.45 NEC 285

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	08467-SURGE PROTECTION REPLACEMENT
Discount Schedule	DE1B
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.26 in (15.9 cm)
Package 1 Width	9.92 in (25.2 cm)
Package 1 Length	2.68 in (6.8 cm)
Package 1 Weight	9.40 lb(US) (4.264 kg)