

Product data sheet

Specifications

SQUARE D



Switch UL508 NEMA 4X IEC309 250V 30A 3P

MD430MI9

! Discontinued

Main

Range	MD50
Product	Motor Disconnect Switch
Current Rating	30 A
Certifications	UL Listed
Enclosure Rating	NEMA 4X/12 valox
Disconnect Type	Non-fusible disconnect switch
Horsepower Rating	10 hp 250 V AC
Included	Conduit hub Grounding
Short Circuit Current Rating	10 kA
Mounting Type	35 mm DIN rail
Number Of Poles	3
Control Type	Selector switch ON-OFF)
Phase	3 phase
For Use With	Plug ME430P9W
Duty Rating	Heavy duty
Wire Size	AWG 12...AWG 8
Wiring Configuration	4-wire

Ordering and shipping details

Category	00056-DISCONNECT - UL508/IEC309
Discount Schedule	DE1
Gtin	00785901599753
Returnability	No
Country Of Origin	DE

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.