





Panelboard interior, NQ, main lugs, 600A, Cu bus, 30 pole spaces, 1 phase, 3 wire, 240VAC, 48VDC

NQ30L6C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,863.00 USD

Main

Panelboard Type	Main lugs
Branch Circuit Breaker Type	QOB
	QOB-VH
	QHB
Busbar Material	Copper

Complementary

Number Of Spaces	30
Enclosure Nominal Height	62 in (1574.80 mm)
Enclosure Nominal Width	20 in (508.00 mm)
Enclosure Nominal Depth	5.75 in (146.05 mm) NEMA 1 6.5 in (165.10 mm) NEMA 3R/5/12
Line Rated Current	600 A
[lu] Rated Interrupted Current	10 kA 22 kA 65 kA
Wiring Configuration	3-wire
Number Of Phases	1 phase
Voltage Rating	240 V AC 48 V DC
Tightening Torque	274.99300.04 lbf.in (31.0733.90 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 274.99300.04 lbf.in (31.0733.90 N.m) 0.080.27 in² (53.48177.3 mm²) (AWG 1/0350 kcmil) 549.98 lbf.in (62.14 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 549.98 lbf.in (62.14 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil) 375.01 lbf.in (42.37 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 375.01 lbf.in (42.37 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil)
Height	45 in (1143.00 mm)
Width	10.44 in (265.18 mm)
Net Weight	7.00 lb(US) (3.175 kg)

Environment

Ctandarda	1.11	
Standards	UL	
	CSA	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1PE1A09151
Discount Schedule	PE1A
Gtin	785901498285
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	7.00 lb(US) (3.175 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	