Product data sheet

Specifications





Brush-type cable entry gasket, PanelSeT SFN, Spacial SF, for electrical enclosure W800mm, set of 2

NSYBCE8

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 33.84 USD

Main

| Range | Spacial |
|---------------------------------------|---------------------------------------|
| Product Or Component Type | Brush gasket |
| Accessory / Separate Part Category | Cable management accessory |
| Device Application | Multi-purpose |
| Range Compatibility | Spacial Spacial SF suitable enclosure |
| Device Composition | 2 gasket |
| Quantity Per Set | Set of 1 |

Complementary

| Mounting Support | Cable gland plate | |
|------------------|---|--|
| Cable Entry | 1 or 2 entries | |
| Fixing Mode | Clipped | |
| Height | 2.76 in (70 mm) | |
| Width | Nominal 31.50 in (800 mm) Real 28.94 in (735 mm) | |
| Depth | 0.98 in (25 mm) | |

Ordering and shipping details

| Category | US10ES180036 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606485130064 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.76 in (7.0 cm) |
| Package 1 Width | 3.15 in (8.0 cm) |
| Package 1 Length | 29.13 in (74.0 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Weight | 15.03 oz (426.0 g) |
|------------------------------|-------------------------|
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 120 |
| Package 2 Height | 41.34 in (105.0 cm) |
| Package 2 Width | 31.50 in (80.0 cm) |
| Package 2 Length | 47.24 in (120.0 cm) |
| Package 2 Weight | 203.27 lb(US) (92.2 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| 9 | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |