# Product data sheet

Specifications





# Spacial CRN plain door w/o mount.plate. H200xW200xD150 IP66 IK10 RAL7035..

NSYCRN22150

Product availability: Stock - Normally stocked in distribution facility

Price\*: 94.91 USD

### Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	7.87 in (200 mm)
Enclosure Nominal Width	7.87 in (200 mm)
Enclosure Nominal Depth	5.91 in (150 mm)
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door 1 lock 2 cable gland plate top and bottom
Door Type	Solid
Mounting Plate Description	Without mounting plate

## Complementary

Body Type	Sides made from a single folded section  Back welded with double profile forming a protected sealed area
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body steel
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	UL cUL DNV-GL
Net Weight	5.56 lb(US) (2.52 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environment**

Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

## Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480212659
Returnability	Yes
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
	1 02
Number Of Units In Package 1	1
Package 1 Height	6.69 in (17.000 cm)
Package 1 Width	8.07 in (20.500 cm)
Package 1 Length	8.46 in (21.500 cm)
Package 1 Weight	5.61 lb(US) (2.544 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	50
Package 2 Height	35.43 in (90.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	306.88 lb(US) (139.200 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations