Product data sheet

Specification





ClimaSys forced vent. IP54, 560m3/h, 230V, with outlet grille and filter G2

NSYCVF560M230PF

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 467.78 USD

Overview

Lead Time

Main	
Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Range Compatibility	Prisma P Prisma G
Type Of Filter	Standard
Flow Rate	Free flow rate with standard filter: 148467.35 Gal/hr(US) (562 m3/h) at 50 Hz Free flow rate with standard filter: 154807.59 Gal/hr(US) (586 m3/h) at 60 Hz
[Us] Rated Supply Voltage	207244 V
Input Voltage	230 V 50/60 Hz

Usually Ships within 4 Weeks

Complementary

Absorbed Power	68 W 50 Hz 85 W 60 Hz
Line Rated Current	0.52 A 50 Hz 0.37 A 60 Hz
Noise Level < At	59 dB
Bearing Type	Ball
Height	External 13.23 in (336 mm)
Width	External 12.44 in (316 mm)
Depth	External 6.34 in (161 mm)
Cut-Out Dimensions	291 x 291 mm
Net Weight	7.05 lb(US) (3.2 kg)
Material	Outlet grille injected thermoplastic (ASA PC)
Color	Outlet grille Gray RAL 7035)
Ambient Air Temperature For Operation	5140 °F (-1560 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Maximum Pressure	140 Pa flow rate 0 m³/h
Connections - Terminals	Terminal block

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP54
Device Composition	1 axial motor
	2 protective grille on the front and rear surfaces
	1 filter front of axial motor
	1 outlet grille front
	1 cut-out template
Condition Of Use	Filter must be cleaned and replaced regularly
	Surrounding environment must be relatively clean
	Outside temperature must be 5 °C lower than inside temperature
	Overfrequent filter replacement should be avoided
	Flow rates depends on the work point, see ProClima software

Ordering and shipping details

	<u> </u>
Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480151323
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.06 in (23 cm)
Package 1 Width	12.60 in (32 cm)
Package 1 Length	13.39 in (34 cm)
Package 1 Weight	7.84 lb(US) (3.554 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	24
Package 2 Height	46.85 in (119 cm)
Package 2 Width	31.50 in (80 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	264.55 lb(US) (120 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information