
Specifications





NSYFCG60

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 56.16 USD

### Main

| Range                                | Spacial           |
|--------------------------------------|-------------------|
| Category                             | Cabling accessory |
| Product Or Component Type            | Rail              |
| Application                          | Multi-purpose     |
| Nominal Dimensions Of The<br>Housing | -                 |

Complementary

| Complemental        | <b>y</b>                        |  |
|---------------------|---------------------------------|--|
| Mounting Location   | Bottom frame of enclosure       |  |
| Range Compatibility | Spacial Spacial SF              |  |
|                     | Spacial Spacial SM              |  |
|                     | Spacial Spacial SFX             |  |
|                     | Spacial Spacial SMX             |  |
| Device Composition  | fixing elements                 |  |
|                     | 1 rail                          |  |
|                     | 2 mounting support              |  |
| Quantity Per Set    | Set of 1                        |  |
| Material            | steel                           |  |
| Surface Finish      | Galvanized                      |  |
| Fixing Mode         | Metal clamp                     |  |
| Adjustment          | Adjustable in depth every 25 mm |  |
| Fixing Center       | 550 mm                          |  |
| Width               | Nominal: 23.62 in (600 mm)      |  |

## Ordering and shipping details

| Category          | US10ES180036  |
|-------------------|---------------|
| Discount Schedule | 0ES1          |
| Gtin              | 3606480064470 |
| Returnability     | No            |
| Country Of Origin | ES            |

## **Packing Units**

| Unit Type Of Package 1       | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1   |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Package 1 Height             | 2.17 in (5.500 cm)        |
|------------------------------|---------------------------|
| Package 1 Width              | 2.17 in (5.500 cm)        |
| Package 1 Length             | 23.43 in (59.500 cm)      |
| Package 1 Weight             | 3.63 lb(US) (1.647 kg)    |
| Unit Type Of Package 2       | P12                       |
| Number Of Units In Package 2 | 40                        |
| Package 2 Height             | 17.72 in (45.000 cm)      |
| Package 2 Width              | 31.50 in (80.000 cm)      |
| Package 2 Length             | 47.24 in (120.000 cm)     |
| Package 2 Weight             | 171.70 lb(US) (77.880 kg) |
|                              |                           |

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

# Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration           |
| China Rohs Regulation    | China RoHS declaration<br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |