

Product data sheet

Specifications



Portable lamp with ON/OFF switch 20 W - 230 V

NSYLAMP0RT

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Main

Range Of Product	Lighting and power sockets
Accessory / Separate Part Category	Lighting accessory
Product Or Component Type	Portable lamp
Device Application	Multi-purpose
Device Composition	lamp power cord

Complementary

[Ue] Rated Operational Voltage	230 V 50-60 Hz
Bulb Base	E27
Bulb Type	Fluorescent
Control Type	Built-in recessed switch
Service Life In Hours	8000 h
Electrical Connection	1 pre-cabled male connector Cable 9.84 ft (3 m)
Mounting Support	Enclosure
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Thalassa Thalassa PLA Thalassa Thalassa PLM Spacial Spacial SFX Spacial Spacial SMX Spacial Spacial SF Spacial Spacial SM
Material	Light gray plastic
Height	10.64 in (270.2 mm)
Width	2.66 in (67.6 mm)
Depth	3.46 in (88 mm)

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Electrical Insulation Class	Class II
Standards	UL 94 IEC 61000-6-4
Ambient Air Temperature For Operation	-4...122 °F (-20...50 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-49...158 °F (-45...70 °C)
-------------------------------------	----------------------------

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
Gtin	3606480467622
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8 cm)
Package 1 Width	4.25 in (10.8 cm)
Package 1 Length	14.37 in (36.5 cm)
Package 1 Weight	27.16 oz (770 g)

Contractual warranty

Warranty	18 months
----------	-----------