Product data sheet

Specifications





Microperforated mounting plate H600xW600 w/holes diam 3,6mm on 12,5mm pitch

NSYMF66

Product availability: Stock - Normally stocked in distribution facility

Price*: 61.37 USD

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 23.62 in (600 mm) W: 23.62 in (600 mm)	
Mounting Location	Step slide Direct fixing on backstuds	
Mounting Plate Description	Microperforated	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set of 1	
Material	galvanised steel	

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Permanent Permissible Load	297.62 lb(US) (135 kg)
Height	22.24 in (565 mm)
Width	21.65 in (550 mm)
Depth	4.92 in (125 mm)
Thickness	0.07 in (1.8 mm)
Net Weight	9.70 lb(US) (4.4 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480183102
Returnability	Yes
Country Of Origin	ES

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.12 in (0.3 cm)
Package 1 Width	21.65 in (55.0 cm)
Package 1 Length	22.24 in (56.5 cm)
Package 1 Weight	9.70 lb(US) (4.4 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations