

Product data sheet

Specifications



Plain mounting plate, PanelSeT SFN, Spacial SF, Spacial SM, for electrical enclosure H2000 W800mm, galvanized steel

NSYMP208

Product availability: Stock - Normally stocked in distribution facility

Price*: 217.20 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 78.74 in (2000 mm) W: 31.50 in (800 mm)
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Device Composition	1 mounting plate 2 sliding shoes
Quantity Per Set	Set of 1
Material	galvanised steel

Complementary

Fixing Mode	By fixing brackets
Maximum Load	300 kg/m²
Permanent Permissible Load	1102.31 lb(US) (500 kg) intermediate position 1322.77 lb(US) (600 kg) back of the enclosure
Height	Fixing centers 72.83 in (1850 mm) Nominal 78.74 in (2000 mm) Real 74.69 in (1897 mm)
Width	Nominal 31.50 in (800 mm) Fixing centers 25.59 in (650 mm) Real 27.40 in (696 mm)
Depth	1.06 in (27 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485126906
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	27.56 in (70.0 cm)
Package 1 Length	75.39 in (191.5 cm)
Package 1 Weight	68.34 lb(US) (31.0 kg)
Unit Type Of Package 2	P2M
Number Of Units In Package 2	20
Package 2 Height	31.50 in (80.0 cm)
Package 2 Width	78.74 in (200.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1413.16 lb(US) (641.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations