
# Product data sheet





## Monobloc perforated plates H400xW600mm with universal perforations 11x26mm

NSYMR46

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 108.64 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
<b>Enclosure Nominal Dimensions</b>	- H: 15.75 in (400 mm) W: 23.62 in (600 mm)
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Telequick perforated
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	steel
Surface Finish	Zinc coated

#### Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Height	13.58 in (345 mm)
Width	21.69 in (551 mm)
Depth	0.59 in (15 mm)
Thickness	0.08 in (2 mm)
Net Weight	3.35 lb(US) (1.518 kg)
Number Of Slots	456
Variant Particularity	Installation in rear of enclosure
Cut-Out Dimensions	11 x 26 mm

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480183669
Returnability	No

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin FR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	13.58 in (34.5 cm)
Package 1 Length	21.69 in (55.1 cm)
Package 1 Weight	3.01 lb(US) (1.366 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	234
Package 2 Height	35.43 in (90.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	734.14 lb(US) (333.0 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations