

Product data sheet

Specifications



Spacial SF/SM double ventilated door - 1200x800 mm

NSYPCV2D128

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Main

| | |
|------------------------------------|---|
| Range | Spacial |
| Accessory / Separate Part Category | Enclosure accessory |
| Product Or Component Type | 19" door |
| Application | Multi-purpose Electronic application |
| For Enclosure Nominal Dimensions | - |
| Mounting Location | Front |
| Range Compatibility | Spacial Spacial SF Spacial Spacial SM |
| Device Composition | 1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 2 door 1 blocking system |
| Quantity Per Set | Set of 1 |

Complementary

| | |
|-------------------|----------------------------|
| Material | sheet steel |
| Color | Gray RAL 7035) |
| Surface Finish | Epoxy-polyester powder |
| Lock Type | Lock 5 mm double bar |
| Number Of Locks | 1 |
| Door Type | Fully Ventilated |
| Door Opening Side | Reversible 120 °) |
| Height | Nominal 47.24 in (1200 mm) |
| Width | Nominal 31.50 in (800 mm) |

Ordering and shipping details

| | |
|-------------------|-------------------------------------|
| Category | 80035-ENCLOSURE SYSTEMS FLOOR MOUNT |
| Discount Schedule | ES1 |
| Gtin | 03606480066580 |
| Returnability | No |
| Country Of Origin | FR |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|