# Product data sheet





Floor standing polyester enclosure, Thalassa PLA, plain door, completely sealed, 1250x750x320mm, IP65, IK10

NSYPLA1273G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 856.13 USD

#### Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLA
Nominal Height	49.21 in (1250 mm)
Nominal Width	29.53 in (750 mm)
Nominal Depth	12.60 in (320 mm)
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door

### Complementary

Body Type	Sealed top and bottom part assembled with side parts
Door Type	Solid front
Number Of Doors	1
Door Opening Side	Reversible 120 °)
Lock Type	4 points lock, 5 mm double-bar
Accessibility For Operation	Rear Front
Removable Parts	Door by hinges Rear panel by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208 UL 508 A

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 2
	NEMA 1
	NEMA 3
	NEMA 12
	NEMA 13
	NEMA 3S
	NEMA 5
	NEMA 3X
	NEMA 3R
Product Certifications	DNV Marine
	Veritas
	UL/cUL listed
Electrical Insulation Class	Class II

### **Environment**

Ip Degree Of Protection	IP65 IEC 60529 completely sealed)
Ik Degree Of Protection	IK10 IEC 62262 plain door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31194 °F (-3590 °C)

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480774638
Returnability	No
Country Of Origin	ES

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	49.61 in (126.0 cm)
Package 1 Width	14.96 in (38.0 cm)
Package 1 Length	30.71 in (78.0 cm)
Package 1 Weight	73.85 lb(US) (33.5 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	3
Package 2 Height	47.24 in (120 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	54.72 in (139 cm)
Package 2 Weight	249.12 lb(US) (113 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations