

Product data sheet

Specifications



Floor standing polyester enclosure, Thalassa PLA, glazed door, completely sealed, 1250x750x320mm, IP65, IK08

NSYPLA1273TG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,157.88 USD

Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLA
Nominal Height	49.21 in (1250 mm)
Nominal Width	29.53 in (750 mm)
Nominal Depth	12.60 in (320 mm)
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door

Complementary

Body Type	Sealed top and bottom part assembled with side parts
Door Type	Transparent front
Number Of Doors	1
Door Opening Side	Reversible 120 °)
Lock Type	4 points lock, 5 mm double-bar
Accessibility For Operation	Rear Front
Removable Parts	Door by hinges Rear panel by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	UL 508 A IEC 62208

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nema Degree Of Protection	NEMA 2 NEMA 12 NEMA 3S NEMA 5 NEMA 1 NEMA 3R NEMA 13 NEMA 3 NEMA 3X
Product Certifications	DNV Marine UL/cUL listed Veritas
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP65 IEC 60529 completely sealed)
Ik Degree Of Protection	IK08 IEC 62262 glazed door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31...194 °F (-35...90 °C)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480774645
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	49.61 in (126.0 cm)
Package 1 Width	30.71 in (78.0 cm)
Package 1 Length	14.96 in (38.0 cm)
Package 1 Weight	74.48 lb(US) (33.785 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	3
Package 2 Height	47.24 in (120 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	57.48 in (146 cm)
Package 2 Weight	304.24 lb(US) (138 kg)

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations