Product data sheet

Specifications





Floor standing polyester enclosure, Thalassa PLA, plain door, completely sealed, 500x500x320mm, IP65, IK10

NSYPLA553G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 471.16 USD

Main

Thalassa
Thalassa PLA
Multi-purpose
Suitable enclosure
PLA
19.69 in (500 mm)
19.69 in (500 mm)
12.60 in (320 mm)
Floor-standing
1 top part 1 bottom part 2 side part 1 rear panel 1 door

Complementary

Body Type	Sealed top and bottom part assembled with side parts
Door Type	Solid front
Number Of Doors	1
Door Opening Side	Reversible 120 °)
Lock Type	2 points lock, 5 mm double-bar
Accessibility For Operation	Front Rear
Removable Parts	Door by hinges Rear panel by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	UL 508 A IEC 62208

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 3S
	NEMA 3
	NEMA 13
	NEMA 5
	NEMA 12
	NEMA 2
	NEMA 1
	NEMA 3X
	NEMA 3R
Product Certifications	Veritas
	UL/cUL listed
	DNV Marine
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP65 IEC 60529 completely sealed)
Ik Degree Of Protection	IK10 IEC 62262 plain door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31194 °F (-3590 °C)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480774911
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	20.08 in (51.0 cm)
Package 1 Width	21.26 in (54.0 cm)
Package 1 Length	14.96 in (38.0 cm)
Package 1 Weight	31.77 lb(US) (14.41 kg)
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	15
Package 2 Height	47.24 in (120 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	65.75 in (167 cm)
Package 2 Weight	489.43 lb(US) (222 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations