

# Product data sheet

Specifications



Floor standing polyester enclosure, Thalassa PLA, plain door, ventilated canopy, 1250x1250x320mm, IP44, IK10

NSYPLAT12123G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,648.86 USD

## Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLAT
Nominal Height	49.21 in (1250 mm)
Nominal Width	49.21 in (1250 mm)
Nominal Depth	12.60 in (320 mm)
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy

## Complementary

Body Type	Open top and sealed bottom part assembled with side parts
Door Type	Solid front
Number Of Doors	2
Door Opening Side	Right and left 120 °)
Lock Type	4 points lock, handle with 5 mm double bar insert
Accessibility For Operation	Top Rear Front
Removable Parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas
Electrical Insulation Class	Class II

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ip Degree Of Protection	IP44 IEC 60529 with ventilated canopy)
Ik Degree Of Protection	IK10 IEC 62262 plain door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31...194 °F (-35...90 °C)

## Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480775253
Returnability	No
Country Of Origin	ES

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	49.61 in (126.0 cm)
Package 1 Width	50.79 in (129.0 cm)
Package 1 Length	14.96 in (38.0 cm)
Package 1 Weight	129.11 lb(US) (58.561 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	52.36 in (133 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	56.30 in (143 cm)
Package 2 Weight	306.44 lb(US) (139 kg)

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations