

Product data sheet

Specifications



Floor standing polyester enclosure, Thalassa PLA, plain door, ventilated canopy, 500x1000x420mm, IP44, IK10

NSYPLAT5104G

! Discontinued

! Discontinued on: Jul 3, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLAT
Nominal Height	19.69 in (500 mm)
Nominal Width	39.37 in (1000 mm)
Nominal Depth	16.54 in (420 mm)
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy

Complementary

Body Type	Open top and sealed bottom part assembled with side parts
Door Type	Solid front
Number Of Doors	2
Door Opening Side	Right and left 120 °)
Lock Type	2 points handle lock, 5 mm double-bar
Accessibility For Operation	Top Front Rear
Removable Parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas
Electrical Insulation Class	Class II

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Ip Degree Of Protection	IP44 IEC 60529 with ventilated canopy)
Ik Degree Of Protection	IK10 IEC 62262 plain door)
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-31...194 °F (-35...90 °C)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480775406
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.65 in (55.0 cm)
Package 1 Width	40.55 in (103.0 cm)
Package 1 Length	17.72 in (45.0 cm)
Package 1 Weight	79.69 lb(US) (36.148 kg)

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile