

Product data sheet

Specifications



HMI encl. Spacial S3CM.
H300xW400xD200IP54 IK10,
RAL7035.Rear door.

NSYS3CM304020

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 623.06 USD

Main

Range	Spacial
Product Name	Spacial S3CM
Application	Human-machine dialogue application
Category	Control enclosure
Enclosure Nominal Height	11.81 in (300 mm)
Enclosure Nominal Width	15.75 in (400 mm)
Enclosure Nominal Depth	7.87 in (200 mm)
Installation Accessory Type	Suspension system
Product Destination	Interface
Device Composition	1 body 1 door with lock 2 rail 1 reinforcement plate 1 front trim frame

Complementary

Body Type	Single piece body
Door Type	Solid
Number Of Doors	Rear 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Rear
Removable Parts	Door by hinges Trim frame by screws 2 rails by screws
Material	Enclosure and front face steel Trim frame aluminium
Surface Finish	epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Front face Gray RAL 7040)
Net Weight	20.16 lb(US) (9.146 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Ip Degree Of Protection	IP54 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

Ordering and shipping details

Category	US10ES180033
Discount Schedule	0ES1
Gtin	3606480212932
Returnability	Yes
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.60 in (32.0 cm)
Package 1 Width	16.54 in (42.0 cm)
Package 1 Length	8.66 in (22.0 cm)
Package 1 Weight	20.16 lb(US) (9.146 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations