# Product data sheet

Specifications





Wall mounted steel enclosure, Spacial S3D, double plain door, without mounting plate, 1000x1000x300mm, IP55, IK10

NSYS3D101030D

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 484.06 USD

#### Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	39.37 in (1000 mm)
Enclosure Nominal Width	39.37 in (1000 mm)
Enclosure Nominal Depth	11.81 in (300 mm)
Door Type	Solid
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
Device Composition	1 body 2 cable gland plate 1 lock 2 door

### Complementary

Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face 2
Door Opening Side	Reversible 120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	steel
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	GL UL
	cUL
	LR BV
	DNV
Net Weight	101.41 lb(US) (46 kg)

### **Environment**

Electromagnetic Compatibility	Electromagnetic field immunity test
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP55 IEC 60529

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480160332
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.78 in (35.0 cm)
Package 1 Width	39.76 in (101.0 cm)
Package 1 Length	40.16 in (102.0 cm)
Package 1 Weight	103.49 lb(US) (46.943 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	3
Package 2 Height	47.24 in (120 cm)
Package 2 Width	40.16 in (102 cm)
Package 2 Length	45.28 in (115 cm)
Package 2 Weight	330.69 lb(US) (150 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations