# **Product data sheet**

Specifications





Wall mounted steel enclosure, Spacial S3D, plain door, with mounting plate, 1200x800x300mm, IP66, IK10

NSYS3D12830P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 545.76 USD

#### Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	47.24 in (1200 mm)
Enclosure Nominal Width	31.50 in (800 mm)
Enclosure Nominal Depth	11.81 in (300 mm)
Door Type	Solid
Mounting Plate Description	Plain
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
<b>Device Composition</b>	1 body 2 cable gland plate 1 mounting plate 1 door with lock

## Complementary

Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure steel Mounting plate galvanised steel
Surface Finish	Enclosure epoxy-polyester powder
Color	Enclosure Gray RAL 7035)
Standards	IEC 62208

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	cUL LR DNV GL UL
Net Weight	134.48 lb(US) (61 kg)

## **Environment**

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP66 IEC 60529

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480159879
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.98 in (35.5 cm)
Package 1 Width	32.48 in (82.5 cm)
Package 1 Length	48.23 in (122.5 cm)
Package 1 Weight	131.84 lb(US) (59.8 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	38.19 in (97.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	48.23 in (122.5 cm)
Package 2 Weight	289.69 lb(US) (131.4 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations